

1999 Fristam FPX-Series Centrifugal Pump

Mfg: Fristam

Model: FPX1161-320

Stock No: NOIP9011

Serial No: FPX1161992322

1999 Fristam FPX-Series Centrifugal Pump. Model: FPX1161-320. S/N: FPX1161992322. Approximate flow rate for new pump is 800 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 12 in. (305 mm). Baldor Electric motor: 50 Hp, 1800 Rpm, 230/460 V, 3 phase. Capable of delivering high volumes and high pressures while handling shear sensitive products, it is the pump of choice for products with viscosities up to 600 cps and process temperatures up to 400°F. The FPX series is well known for quiet, efficient, low maintenance operations. Inlet/Outlet: (2) 4 in. S-line fittings. Overall dimensions: 3 ft. 3 in. L. x 1 ft. 9-1/2 in. W. x 2 ft. 1-1/2 in. H.(ACN62).





