

1997 S.A. Armstrong LTD Shell & Tube Heat Exchanger – 284 Sq. Ft.

Mfg: S.A. Armstrong LTD

Model: W-1214-45-1

Stock No: MXMP01.7a

Serial No: 76618

1997 S.A. Armstrong LTD Shell & Tube Heat Exchanger. Model: W-1214-45-1. Serial No: 76618. Natl. Bd. no: 4902. Estimated heat exchange surface area: 284 square feet. 4-pass design with 104 tube holes. 20 gauge copper tubes, 3/4 in. diameter. MAWP: tube side: 125 psi at 375°F, shell side: 150 psi at 375°F. MDMT: tube side: 35°F at 125 psi. Shell side: 35°F at 150 PSI. Inlet/outlets: 4 in. threaded. Overall dimensions: 14 ft. 8 in. L x 1 ft. 4-1/2 in. W x 1 ft. 9 in. H.

