

Ozaf Mechanical Feeder - (96) Compartments

Mfg: Ozaf

Model:

Stock No.: NOI8048

Serial No.:

Ozaf Mechanical Feeder. Unit has (96) compartments and is constructed of polyethylene. Inside straight wall dimensions: 3 ft. 11 in. dia. x 9 in. H. Infeed chute dimensions: 1 ft. 1/2 in. L x 5 in. W. x 5 in. H. (2) Penta DC motors. Model: MP100A20. S/N: ITN. Power supply: 180 V, 2 amps, 60 Hz, single phase. Mechanical feeders make it possible to convey and unscramble different types of items in a wide range of shapes such as caps, ring nuts, pumps, atomizers. Infeed height: 3 ft. Exit height: 4 ft. 3 in. Overall dimensions: 5 ft. 5 in. L x 4 ft. 5 in. W x 5 ft. 3 in. H.







