


3.64 PSI MINIMUM LIQUID FEED PRESSURE  
 REQUIRED ABOVE COIL SUCTION PRESSURE,  
 AT LIQUID INLET.



SO 5989 ITEM: A QTY: 1

UNIT DATA:  
 CASING-GLV SHEET  
 PAN-INSUL w/GLV  
 SHEET COVER

FAN DATA:  
 20,400 CFM @ 0" ESP  
 (5) 24" DIR DRV PROP FANS  
 (5) 1/3 HP 1200 RPM TEAO  
 ATO 480-3-60

PERFORMANCE DATA:  
 12.76 TON @ 11° TD  
 FEED: LR, BTM, NH<sub>3</sub>, HOT GAS  
 DEFROST  
 33° F ROOM  
 22° F COIL  
 20° F LIQUID @ 3:1 RATE

CO 524-64  
 CHILFLO UNIT COOLER  
 for  
 BALCO, INC.  
 for  
 H.P. HOOD  
 BOSTON, MA



B-1490007

D.M.J.N SCALE 1/2" = 1"  
 C DATE 6-13-84

B-1490418