

Fisher Pneumatic Valve Positioner

Mfg: Fisher

Model:

Stock No. OI268.

Serial No. 9524921

Fisher Pneumatic Valve Positioner. S/N: 9524921. Type: 1052/V100/36101. Size: 2. ANSI flange: Class 600. Body rating: 1480/100 psig. Maximum pressure differential: 740/100 psig/°F. Maximum temperature: 405° F. Body: VCB VEE-Ball. Seat: TCM. Shaft stem: 17-14PH. Ball disc: 317 CRPL. Bearing: 316 TFF. Rotation: 90°. Actuator size: 30. Order No: P-59450. Tag: TCV-3-859. Fisher Controls Electro Pneumatic Transducer, Type: 546, S/N: 9482220, output pressure: 3 to 15 psi, recommended supply pressure: 20 psi, maximum supply pressure: 50 psi. Inlets/outlets: (2) 2 in. dia. flanged ports. Overall dimensions: 2 ft. 8 in. L x 1 ft. 8 in. W x 2 ft. 6 in. H.

