

PACKO Centrifugal Pump

Mfg: PACKO


Model:

Stock No: NOIP1120

Serial No: 17928

PACKO Centrifugal Pump. Type: SETFP2TA/32-125/BEL. No. 17928. Baldor motor: 3.2 kw, 1725 rpm, 230/460 v, 13.2/6.6 a, 60 Hz, 3 phase. (1) 5-1/2 in. dia. impeller. Inlets/outlets: (1) 3 in. ACME, (1) 2 in. ACME, (1) 1/2 in. MNPT. Overall dimensions: 2 ft. 1 in. L x 1 ft. 1 in. W x 1 ft. 6 in. H.





PACKO DIKSMUIDE BELGIUM

TYPESE TFP2TA/32-125/BEL

Mat-code: 0-140

Cust. code: 593-2196

H: m Nr: 17928

Q: m³/h ←

BALDOR
I.E.C. INDUSTRIAL MOTOR
BALDOR ELECTRIC CO.
FT. SMITH, AR. MFG. IN U.S.A.

CAT. NO.	KVN30100		
SPEC.	36H938UG1561		
IEC FRAME	0112ND	KW	3.7
VOLTS	230/460		
AMPS	13.2/6.6		
R.P.M.	1725	I.P.	50
HZ	50	PH	CLASS F
SER. F.	1.14	DES	CODE J
WOM EFF	83.4	% PF	80
RATING	100% AMP-FRONT		
CC	USABLE AT 200V		
INSULATION	DL	OOB	15
CFR	15		