

Mission Centrifugal Pump

Mfg: Mission

Model:

Stock No.: NPPC224

Serial No.:

Mission Centrifugal Pump. Size: 3 x 1.5 x 10. Flow rate for new pump is 140 gpm with required horsepower and at 90 ft. TDH. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 10 in. Product contact areas are of 316 SS construction. Pump features double mechanical seals with water flush. Reliance Motor: 7.5 hp, 1,760 rpm, 230/460 V, 18/9 amps, 60 Hz, 3 phase. Overall dimensions: 4 ft. L x 1 ft. 6 in. W x 1 ft. 8 in. H. (ACN67a).

