

Warren Rupp/SandPiper Aluminum Diaphragm Pump

Mfg: Warren Rupp/SandPiper

Model: SA3-A

Stock No. OI09

Serial No.

Warren Rupp/SandPiper Aluminum Diaphragm Pump.

- Model SA3-A
- 4 in. flanged inlet/ outlet
- Adjustable flowrate: 0 to 260 gpm
- Solids handling up to nearly 3 in. heads up to 125 psi or 289 ft. of water.
- Overall dimensions: 35 in. L x 16 in. W x 33 in. H.
- Flap valve SA Series Sandpiper® pumps are especially recommended for slurries and liquids with suspended solids.
- Flap-valves allow passage of suspended line-size solids without damage.

