

Durco / Durion Centrifugal Pump

Mfg: Durco / Durion

Model: Mark II

Stock No. OIP028.

Serial No. 165830

Durco / Durion Centrifugal Pump. Model: Mark II. S/N: 165830. Size: 3x2 - 7. Stainless steel impeller, casing, and shaft. Capacity: 300 gpm @ 160 head feet (~70 psi using specific gravity of water = 1). Displacement per Revolution: 0.085. Seal Option: double mechanical with water flush. Impeller: 7 in. dia. Baldor Motor, 1.5 HP, 3,450 rpm, 208-230/460 V, 60 Hz, 19-18/9 amps, 3-phase. Inlet: 3 in. flange. Outlet: 2 in. flange. Overall Dimensions: 3 ft. 6 in. L x 1 ft. 1 in. W x 1 ft. 8 in. H.

