

## Stainless Steel Incline Conveyor with Hopper

**Mfg:**

**Model:**

**Stock No.: OI121**

**Serial No.:**

Stainless Steel Incline Conveyor Belt. Conveyor dimensions: 7 ft. 6 in. L x 8-1/2 in. W. Cleat height: 1-1/2 in. Distance between cleats: 1 ft. Maximum hopper dimensions: 2 ft. 2 in. W x 1 ft. 8 in. H (back) . Minimum Hopper: 1 ft. 5 in. W x 10-1/2 in. H (front). Baldor motor, 1 hp, 1750 rpm, 90 V, 10 amps, 60 Hz, single phase. Conveyor infeed height: 3 ft., conveyor exit height: 9 ft. Overall dimensions: 7 ft. 2 in. L x 3 ft. W x 9 ft. H.



