

Young Machinery Co. Stainless Steel Rotary Mill – 25 HP

Mfg: Young Machinery Co.

Model: 624

Stock No.: OI250b.365

Serial No.: 428

Young Machinery Co. Stainless Steel Rotary Shear Mill/Cutter – Hammer mill. S/N 428, Size: 624. S.O. No: 1952. Cust. No: 5-121. Constructed for mixing ingredients of different weights, bulk densities and shapes, and may be used on either a continuous blending or batch type blending arrangement. Mild steel frame. Mounted on four casters for easy maneuverability. Infeed hopper dimensions: 24 in. L x 17 in. W. Lincoln AC Motor, 25 hp, 1750 rpm, 721 Final rpm, 3 phase, 230/460 V, 64/32 amps. Inlets: (1) 24 in. L x 8 in. W infeed throat. Outlets: (1) 3 in. dia. S-Line fitting. Overall dimensions: 58 in. L x 54 in. W x 58 in.H.



