

## Fristam FP-Series Centrifugal Pump

**Mfg: Fristam**

**Model:**

**Stock No. OIP103.**

**Serial No. 12122759**

Fristam FP-Series Centrifugal Pump. S/N: 12122759. Capacity: 150 gpm. Impeller diameter: 5.00 in. Seal option: double mechanical with flushing. Baldor Industrial Motor, 5 hp, 3450 rpm, 208-230/460 V, 13-12/6 amps, 60 Hz, 3 phase. The FP-Series is the original Fristam pump with established the standard for high performance centrifugals. These heavy-duty, high performance sanitary centrifugal pumps handle the most demanding applications such as vacuum withdrawal from evaporators, viscous, hot, or abrasive products. Completely CIP-and SIP-able. Inlets: (2) 2-1/2 in. dia. S-line. Outlets: (1) 1-1/2 in. dia. S-line. Overall dimensions: 29 in. L x 13 in. W x 18-1/2 in. H.



