

Fristam FP-Series Centrifugal Pump

Mfg: Fristam

Model: FP742

Stock No. OIP104.

Serial No. 42122495

Fristam FP-Series Centrifugal Pump. Model: FP742. S/N: 42122495. Capacity: 100 gpm. Impeller diameter: 5-3/4 in. Seal option: double mechanical with flushing. Motor, 230 V, 7.5 amps. The FP-Series is the original Fristam pump with established the standard for high performance centrifugals. These heavy-duty, high performance sanitary centrifugal pumps handle the most demanding applications such as vacuum withdrawal from evaporators, viscous, hot, or abrasive products. Completely CIP-and SIP-able. Inlets: (1) 2-1/2 in. dia. S-line fittings. Outlets: (1) 2 in. dia. S-line fittings. Overall dimensions: 29 in. L x 13 in. W x 18-1/2 in. H.



