

Fristam FPX-Series Sanitary Centrifugal Pump

Mfg: Fristam

Model: FPX 3532/165

Stock No. OIP135.

Serial No. 353268098

Fristam FPX-Series Sanitary Centrifugal Pump. Model: FPX 3532/165. S/N: 353268098. Nominal Capacity: 400 gpm @ 85 tdh (~37 psi using specific gravity of water = 1). Maximum Speed: 3500 rpm. Displacement per Revolution: 0.114 gal. Impeller diameter: 6 in. (155 mm). 316 Stainless Steel Interior Components. Seal Option: Single mechanical, chrome oxide/carbon. The FPX-series sanitary centrifugal pump has become an industry standard for most general applications. Capable of delivering high volumes and high pressures while handling shear sensitive products, it is the pump of choice for products with viscosities up to 600 cps and process temperatures up to 400°F. The FPX-series is well known for quiet, efficient, low maintenance operations. Typical applications: bottling, cleaning applications/CIP, de-alcoholization, distillation, emulsifying, evaporation, mechanical separation, reverse osmosis, in-line mixing, water conditioning, transfer filtration, extraction, dosing, dialysis, de-gassing, carbonizing, homogenizing, fermentation. Inlet: (1) 2 ½ in. dia. S-line fittings. Outlet: (1) 1 ½ in. dia. S-line fittings. Overall dimensions: 2 ft. 3 in. L x 1 ft. 1 in. W x 1 ft. 3 in. H.



