

Fristam FP-Series Centrifugal Pump

Mfg: Fristam

Model: FP722

Stock No.: OIP106

Serial No.: 221221174

Fristam FP-Series Centrifugal Pump. Model: FP722. S/N: 221221174. Flow rate for new pump is 80 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 5 in. (130 mm). Double mechanical with water flush seals. Baldor industrial motor, 5 hp, 3450 rpm, 208-230/460 V, 13-12/6 amps, 60 Hz, 3 phase. Applications include but are not limited to: bottling, cleaning applications/CIP, de-alcoholization, distillation, emulsifying, evaporation, mechanical separation, reverse osmosis, inline mixing, water conditioning, transfer filtration, extraction, dosing, dialysis, de-gassing, carbonizing, homogenizing, and fermentation. Inlets: (1) 2 in. dia. S-line. Outlets: (1) 1-1/2 in. dia. S-line. Overall dimensions: 2 ft. 3 in. L x 11 in. W x 1 ft. 4-1/2 in. H. (ACN32).



