

## Frick Screw Compressor Package – 150 HP

**Mfg: Frick**

**Model: RWB II 60**

**Stock No: PCNY04**

**Serial No: S0140FFMPLHAA3**

Frick RWB II 60 screw compressor package. Model: RWB II 60. S/N: S0140FFMPLHAA3. Refrigerant: last used with R-717 (Ammonia). Maximum speed: 3600 rpm. Compressor displacement: 445 m<sup>3</sup>/h. Cooling capacity: 363 kW. Max design pressure: 360 psig. Toshiba high efficiency drive motor. Model: 1502VLG3UD, S/N: 7900178A, 150 hp, 3540 rpm, 230/460 V, 348/174 amps, 60 Hz. 3 phase. Oil separator, S/N: MC87606, MAWP: 300 psig @ -20 to 200°F. Vessel: Shell side MAWP: 300 psig @ -20 to 300°F. Frame: 405TS. Tuthill oil pump with Doerr electric motor, ¾ hp, 1725/1425 rpm, 208-220/460 V, 2.7/1.35 amps, 60/50 Hz, 3 phase. Frick RWB II plus control panel: S.O: 262214. Inlet: (1) 4 in. dia. pipe. Outlet: (1) 3 in. dia. pipe. Inlets / outlets have been capped. Overall dimensions: 11 ft. 4 in. L x 4 ft. W x 8 ft. H.. Compressor run time: 6696.4 hours hrs. (ACN553-87).









