

Tri Clover C-Series Centrifugal Pump

Mfg: Tri Clover

Model: C218TF18T-S

Stock No. OIP155.

Serial No. G2747

Tri Clover C-Series Centrifugal Pump. Model: C218TF18T-S. S/N: G2747. Capacity: 30 gpm @ 52 tdh (~23 psi using specific gravity of water = 1). Displacement per Revolution: 0.02 gal. Impeller diameter: 7 in. Louis Allis Electric Motor, 2 hp, 1740 rpm, 230/460 V, 6.2/3.1 amps, 60 Hz, 3 phase. The C-series pump is the original, all-purpose, sanitary process centrifugal pump. Its practical design and flexibility have provided processors with strong performances in thousands of applications. A great value, the C-series pump maintains an integral Clean-In-Place design as standard. Inlets: (1) 3 in. dia. ACME fitting. Outlets: (1) 1 ½ in. dia. ACME fitting. Overall dimensions: 1ft. 8 in. L x 1 ft. W x 1 ft. 1 in. H.



