

**Reco / Howden WRV 204/1.1 Rotary Screw Compressor Package – 250 HP**

**Mfg: Reco / Howden**

**Model: MK5D/WRV 204/11050/1112**

**Stock No: 150.PMI450a.5**

**Serial No: JH2840**

Reco / Howden WRV 204/1.1 Rotary Screw Compressor Package. Model: MK5D/WRV 204/11050/1112, S/N: JH2840. Refrigerant: Last used with R-717 (ammonia). Vi setting: 5.0. Displacement: 568 cfm. General Electric motor, Model: 5K445AK158, S/N: KH481039, 250 hp, 3560 rpm, 460 V, 60 Hz, 3 phase, FLA: 284. DEWCO vertical oil separator, S/N: V-421, Nat'l Bd: 276, MAWP: 300 psig at 250°F. Separator dimensions: 24 in. O.D. x 6 ft. H. Reco control panel. Compressor run time: 12,299 hrs. Overall dimensions: 12 ft. 9 in. L x 4 ft. 3 in. W x 7 ft. 10 in. H.





NATIONAL BOARD No. 276  
DEWCO DODD ENGINEERING  
TULSA, OKLAHOMA & WELDING CO.  
DESIGN PRESSURE 300 PSI @ 250 °F  
MFR'S SERIAL No. V-421 YEAR 1979  
24" O.D. X 6'-0" H. FF  
VERT. OIL SEPARATOR  
12157-21