

Goulds Sanitary Centrifugal Pump

Mfg: Goulds

Model:

Stock No. OIP156.

Serial No.

Goulds Sanitary Centrifugal Pump. John Crane double mechanical seals. Impeller diameter: 9 in. Baldor Industrial Motor, 3 hp, 1725 rpm, 208-230/460 V, 8.5-8.2/4.1 amps, 60 Hz, 3 phase. Inlet: (1) 2 in. dia. flanged port. Outlet: (1) 1 in. dia. flanged port. Overall dimensions: 3 ft. 9 in. L x 1 ft. 1 in. W x 1 ft. 9 in. H.





INDUSTRIAL MOTOR

THREE PHASE

CAT. NO.	M3611T		
SPEC.	35L100Y334		
FRAME	182T	SER.	F1194
H.P.	3	TE	
VOLTS	208-230/480		
AMPS	8.5-8.2/4.1		
R.P.M.	1725		
HZ	60	PH	3 CLASS F
SER. F.	1.15	DES	B CODE 3
NEMA NOM. EFF.	84 %	P.F.	82 %
RATING	1.5 AMP-0.015		

BALDOR ELECTRIC CO.
FT. SMITH, ARK.
MADE IN U.S.A.

