

## Waukesha 320 Positive Displacement Pump

**Mfg: Waukesha**

**Model: 320**

**Stock No: RCJF105.27a**

**Serial No: 170098 95**

Waukesha Model 320 Positive Displacement Pump. Model: 320. S/N: 170098 95. Flow rate for new pump is 450 gpm with required horsepower and pressure. Maximum pressure: 200 psi. Maximum speed: 600 rpm. Temperature range: -40°F to 300°F. Baldor Electric motor: 25 hp, 1760 rpm, 230/460 V, 64/32 A, 60 Hz, 3 phase. SM-Cyclo drive: model: H 3165 SB, 13:1 ratio, 26.4 input hp, 11,400 output torque. Features include ease of cleaning and disassembly, three-way mounting options, and non-galling, Waukesha "88" alloy rotors. (2) rotors 9-5/8 in. dia. Pump and drive are mounted on a mild steel base. (2) ANSI Inlet/Outlet flanges: 6 in. dia. 8 mounting holes: 3/4 in. dia. Adjacent distance : 3-3/4 in. Opposite distance : 9-1/2 in. Unit weight: 1560 lbs. Overall dimensions: 6 ft. 10-1/2 in. L. x 1 ft. 11-1/8 in. W. x 2 ft. 1-1/2 in. H.









