

1993 Reco / Frick RWB II 177B Rotary Screw Compressor Package – 125 HP

Mfg: Reco / Frick

Model: GDSH233S0045 / RWB II 177B

Stock No.: 265.PMI423a.12a

Serial No.: GDSH233S0045

1993 Reco / Frick RWB II 177B Rotary Screw Compressor Package. Model / Serial: GDSH233S0045. Same package as the Frick RWBII-177B. Compressor motor: 125 hp, 460 V, 3 phase, 60 Hz. Reco Oil separator, MAWP: 150 psi @ 300 °F, MDMT -20 °F @ 150 psi, hydro test pressure 225 psi. Oil separator dimensions: 29-1/2 in. dia. x 10 ft 6 in. L. Oil separator inlets/outlets: (1) 6 in. pipe (gas inlet), (1) 4 in. pipe (gas outlet), (1) 11 in. x 15 in. manway, (2) 3 in. oil heaters. Dual oil filter assembly. Thermosyphon oil cooler. Variable Vi setting: 2.2 – 5.0. Displacement: 1,042 cfm. Compressor run time: 53,840 hrs. Overall dimensions: 12 ft. 4 in. L x 5 ft. W x 6 ft. 10 in. H. CF





