

Creamery Package Rota-Pro Swept Surface Heat Exchanger

Mfg: Creamery Package

Model:

Stock No. RCPK545.6a

Serial No.

Creamery Package Rota-Pro Swept Surface Heat Exchanger. Heating surface area: 9.5 ft. sq/cylinder. Standard ASME cylinder jackets are provided for heating with water or steam media up to 450 °F or cooling with water, brine, glycol or other suitable liquid media. Inner cylinder dimensions: 6 in. dia x 48 in. L. Chrome plated nickel barrel. Rotating dashers, with fixed scraper blades, continuously sweep the cylinder surface clean of product, simultaneously producing a highly desirable level of product mixing and agitation contributing to consistency in final product identity. Reliance Electric Motor, 15 hp, 1760 rpm, 230/460 V, 40/20 amps, 60 Hz, 3 phase. Reliance Electric Motor, 10 hp, 1755 rpm, 230/460 V, 27/18.5 amps, 60 Hz, 3 phase. Inlets: (2) 3/4 in. dia. ports, (1) 2 in. dia. media pipe, (1) 2-1/2 in. dia. S-line fitting (product). Outlets: (1) 1 in. dia. pipe (media), (1) 2-1/2 in. dia. S-line fitting (product). Overall dimensions: 88 in. L x 51 in. W x 65 in. H.

Heat Exchange Barrels, S/N's: 8044, 8039, and 8045, Nat'l Bd: 4935, 4936, and 4937, MAWP @ 75 °F: 150 psi, MDMT @ 150 psi: 32 °F.





