

Full-Sweep Agitator with High-Speed Shear Mixer

Mfg:

Model:

Stock No. RFPM1603.4a

Serial No.:

Full-Sweep Agitator with High-Speed Shear Mixer Mounted on Stainless Steel Bridge. Agitator bridge has a 35° decline. Blade sweep: 58 in. Sew-Eurodrive Motor, 5 hp, 1680 rpm, 230/460 V, 13.6/6.8 amps, 60 Hz, 3 phase. Sew-Eurodrive Gear Reducer, 94.9 ratio, 18 rpm (final). High-Speed Shear Mixer, impeller diameter: 6 in., stator diameter: 6-1/4 in. U.S. Motor, 10 hp, 3500 rpm, 230/460 V, 24.4 amps, 60 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. S-line fitting, (2) 4 in. dia. S-line fittings. Overall dimensions: 70 in. L x 24-1/2 in. W x 91 in. H.



