

Cherry Burrell 3x12 Scraped Surface Votator with Moyno Pump

Mfg: Cherry Burrell

Model: 1C312L

Stock No. RCPK628.14a

Serial No. 35526VA

Cherry Burrell 3x12 Scraped Surface Votator with Moyno Pump. Model: 1C312L. S/N: 35526VA. Shell MAWP: 400 psi @ 365 °F. Jacket MAWP: 150 psi @ 365 °F. Baldor Industrial Motor (votator): 3 hp, 1140 rpm, 208-230/460 V, 10.2-9.6/4.8 amps, 60 Hz. Renold Motor Drive, size: GM2D, ratio: 3-1/4 to 1, final rpm: 350. Typical applications are heating and cooling cheese sauce, pudding, caramel, deboned meat, pet food, and fruit products. Control panel, start/stop switches, and stainless steel frame with (4) casters for easy positioning. Inlet: (1) 2 in. threaded fitting (female). Outlet: (1) 1-1/2 in. 'S' line fitting. Overall dimensions: 62 in. L x 23 in. W x 77 in. H.

Moyno pump, model: 1FG3, type: SSQ, S/N: AS56789, capacity: 4 gpm @ 513 rpm. Typical application (pump) are bread dough & bakery products, sauces, juices & jellies, meat & dairy products. Cyncro Gear motor (pump), 1.1 & 2 hp, 1710 rpm, 230/460 V, 4.8/2.4 amps, 3 phase, 60 cycle, ratio: 3.33, final rpm: 513. Start/stop pump motor switches. Pump inlet/outlet: 2 in. threaded female.



