

## Waukesha 130 Positive Displacement Pump

**Mfg: Waukesha**

**Model: 130**

**Stock No. RFPM051.15**

**Serial No. 13310 SS**

Waukesha 130 Positive Displacement Pump. Model: 130. S/N: 13310 SS. Capacity: 106.85 gpm. Displacement per revolution: 0.254 gallon. Nominal capacity: 150 gpm. Maximum rpm: 600. Pressure range up to 200 psi. Baldor Electric Motor, 7-1/2 hp, 1725 rpm, 208-230/460 V, 21.5-20/10 amps, 60 Hz, 3 phase. Dodge APG Gear Drive, ratio: 4.1, final speed: 420.7 rpm, torque: 3084 lbs. The 130's non-galling '88' alloy rotors provide minimum breakage on fluids with discrete particles such as diced tomato products. Waukesha sanitary pumps feature easy cleaning and disassembly. Typical applications: bakery, beverage, canning, confectionary, cosmetics, dairy, meat packaging, and pharmaceutical industries. Inlets/outlets: 3 in. dia. S-line fittings. Overall dimensions: 53 in. L x 16 in. W x 20 in. H.









