

**1991 Vilter Recirculating Tank – 36 in. Dia. x 10 ft. L**

**Mfg: Vilter**

**Model:**

**Stock No: RGMB120.2**

**Serial No: F66684-2**

1991 Vilter Recirculating Tank – 520 Gallon. S/N: F66684-2. Nat'l Bd: 37382. MAWP: 250 psig @ 400°F. MDMT: -20°F @ 250 psi. Refrigerant: R-717 (Ammonia). Radius: 2:1 elliptical ends. Inside straight wall dimensions: 36 in. Dia. x 10 ft. L. Pump. (2) Buffalo Pumps. S/N: 91430108-002. GPM: 26.9. (2) Motor: 3 hp, 3500 rpm, 230/460 V, 9.1/4.5 amps, 60 Hz, 3 phase. Oil Pot: Nat'l Bd: 42787. S/N: 45561. MAWP: 300 psi @ 650°F. MDMT: -20°F @ 300 psi. Hansen Technologies Vari-Level Panel. Inlets/Outlets: (3) 1 in. dia. port. (3) 1 ½ in. dia. port. (2) 2 in. dia. port. (2) 4 in. dia. port. (1) ¾ in. dia. port. (2) 3 in. dia. port. Overall Dimensions: 13 ft. 5 in. L x 7 ft. W x 10 ft. 5 in. H.





