

SIHI Liquid Ring High Performance Vacuum Pump

Mfg: SIHI

Model: LOHB 2704 BN 001 01 2

Stock No.: RFPM518.13a

Serial No.: 2894 151

SIHI Liquid Ring High Performance Vacuum Pump. Model: LOHB 2704 BN 001 01 2. S/N: 2894 151. Capacity: 27 in. Hg @ 25 cfm (using dry air). Westinghouse Motor, 3 hp, 1730 rpm, 230/460 V, 9.4/4.7 amps, 60 Hz, 3 phase. SIHI pumps offer higher vacuum, operational safety, entrained liquid handling, and low vibration and noise levels. The vacuum pumps have one moving part, the impeller and shaft assembly, and no internal metal-to-metal contact. Typical application areas: Chemical, petro-chemical and pharmaceutical, Plastics, Wood/Timber processing, Food, dairy and beverage, Medical, Energy Production, Mining, Water treatment. Inlets/outlets: (2) 1-1/2 in. dia. suction and discharge ports. Overall dimensions: 3 ft. L x 1 ft. 3 in. W x 2 ft. 11-1/2 in. H.(ACN27).



