

Fristam FPX-Series Centrifugal Pump

Mfg: Fristam

Model: FPX-1151-260

Stock No. RLOL718.8

Serial No. 115174060

Fristam FPX-Series Centrifugal Pump. Model: FPX-1151-260. S/N: 115174060. Capacity: 720 gpm @ 32 psi @ 72 tdh. Impeller diameter: 9-1/2 in. Baldor Industrial Motor, 25 hp, 1760 rpm, 230/460 V, 64/32 amps, 60 Hz, 3 phase. Features of FPX-series pumps are: gentle product handling, internal seal for longer seal life, CIP-able and SIP-able, capable of product temperatures up to 400 °F. Great for beverage, syrup, creams, and milk. Inlets/outlets: (2) 4 in. dia. S-line fittings. Overall dimensions: 38 in. L x 25 in. W x 20-1/2 in. H.



