

Bell & Gossett "SU" Series Shell and Tube Heat Exchanger – 100 Sq. Ft.

Mfg: Bell & Gossett

Model:

Stock No: RGMB115C

Serial No:

Bell & Gossett "SU" Series Shell and Tube Heat Exchanger. Estimated heat transfer surface area: 100 sq. ft. 2 pass design. Design pressure shell and tube sides: 150 psi @ 375°F. Inlets/Outlets: (2) 1-1/2 in. dia. port. (2) 2-3/4 in. dia. port. Overall dimensions: 8 ft. 7 in. L x 1 ft. W x 2 ft. 11 in. H.



