

1994 Vilter VSS-601 Rotary Single Screw Compressor Package - 250 HP

Mfg: Vilter

Model: VSS601A025224APAAAN

Stock No: RPCN073.20

Serial No: 3194

1994 Vilter VSS-601 Rotary Single Screw Compressor Package. Model: VSS601A025224APAAAN. S/N: 3194. Order No: K69111. Refrigerant: Last used with R-717 (ammonia). Nominal capacity: 214.7 tons at 227.9 BHP with a 20°F suction temperature and 95°F condensing temperature. Toshiba electric motor, 250 hp, 3575 rpm, 230/460 V, 560/280 amps, 60 Hz, 3 phase. Variable Vi setting: 2.2 to 5.0. Displacement: 568 cfm. Test pressure: 450 psig. 1994 Vilter oil separator. S/N: 3-66326-1. National Board: 40113. MAWP: 300 psig at 400°F. MDMT: -20°F at 300 psig. Straight-wall dimensions: 2 ft. dia. x 11 ft. 5 in. L. Approximate capacity: 280 gallons. Viking pump. Model: 2501A. S/N: 11647038. Marathon electric motor. 3/4 hp, 1750 rpm, 90 V, 7.6 amps, 60 Hz, 3 phase. Viking pump. Model: 2954J. S/N: 11657051. Lincoln electric motor. 3/4 hp, 1725 rpm, 230/460 V, 2.8/1.4 amps, 60 Hz, 3 phase. Vilter control panel. Hoffman control panel. Inlet: (1) 4 in. dia. (refrigerant suction). Outlet: (1) 4 in. dia. (refrigerant suction). Estimated shipping weight: 6,410 lbs. Overall dimensions: 13 ft. L x 4 ft. 10 in. W x 7 ft. 3 in. H. Compressor run time: 60,733 hrs. (ACN815)

Westinghouse Motor Starter Control Panel- 250 HP. Cat. No: R896S5AW1X F940429. Drawing: VW12332. Models: C702T3. Reference No: 022988. Power supply: 460 V, 280 FLA, 60 Hz, 3 phase. Overall dimensions: 3 ft. L x 2 ft. W x 6 ft. 8 in. H.







