

Paco Centrifugal Pump - 1600 GPM

Mfg: Paco


Model:

Stock No: RGMB169

Serial No: 97A0012001-B

Paco Centrifugal Pump-25 hp. S/N: 97A0012001-B. Capacity: 1600 gpm. TDH: 40 ft. Impeller diameter: 8.50 in. Motor: Baldor Industrial motor. 25 hp, 1760 rpm, 230/460 V, 64/32 amps, 60 Hz, 3 phase. Inlet: 8 in. dia. port. Outlet: 6 in. dia. port. Overall dimensions: 3 ft. 8 in. L x 2 ft. 3 in. W x 4 ft. 2 in. H.





INDUSTRIAL MOTOR			
CAT. NO.	10005736		
SPEC.	10005736		
FRAME	200UR	SER.	96106
H.P.	25 HP		
VOLTS	230/460		
AMPS	54/32		
R.P.M.	1780		
PH	50	PI	3 CLASS B
DEF. P.	1.75	DEF	B CODE F
NOM. EFF.	88.5%		82%
MFG. BY BALDOR ELECTRIC CO. ARK. U.S.A.			