

AMT Centrifugal Pump

Mfg: AMT

Model: 490D-98 ; 490B-98

Stock No.: RPCN205D

Serial No.:

AMT Centrifugal Pump. Model: 490D-98, 490B-98. Impeller diameter: 5-1/2 in. WEG Motor, 2 hp, 3440 rpm, 208-230/460 V, 5.5-5.15/2.58 amps, 60 Hz, 3 phase. Inlets: (1) 2 in. dia. port. Outlets: (1) 1-1/2 in. dia. port. Overall dimensions: 1 ft. 3-1/2 in. L x 10 in. W x 9 in. H.





EIXO EM AÇO INOXIDÁVEL
STAINLESS STEEL SHAFT

| | |
|---|---------------------|
| PH 3 D58J | HP (kW) 2.0(1.50) |
| RPM 3440 | DUTY CONT |
| 208-230/480 V | 60 Hz SR 1 15 |
| 5.50-5.15/2.58 A | NSLF Δ 80 KAMB 40 C |
| SFA | ENCL TEFC |
| EFF% 82.50 | PF 0.88 CODE L |
| 1.05F @ 208V | DES A |
| 50Hz 1.5hp 190/380V 5.0/2.5A 2880RPM SF 1.0 | |

WEP
 MADE IN BRAZIL
 070500573
 0402705
 LA 9034
 50236558 JP-68-J-36HP
 MOD: NUTETC04AK-002202E

LOW VOLTAGE
 T4 T5 T6
 T7 T8 T9
 X1 L1 L2 L3

HIGH VOLTAGE
 T4 T5 T6
 T7 T8 T9
 Y L1 L2 L3