

Stainless Steel Scew Auger Conveyor

Mfg:

Model:

Stock No. RWDG074.7a

Serial No.:

Stainless Steel Scew Auger Conveyor. Scew auger dimensions: 8-1/2 in. x 20 ft. L. Pitch: 9 in. Housing diameter: 9 in. Lincoln AC Motor, 1 hp, 1735 rpm, 230/460 V, 34/17 amps, 60 Hz, 3 phase. Dorris Motor Drive, 15 ratio, 115 rpm (final). Inlets/outlets: (3) 9-1/2 in. L x 7 in. W discharge doors. Overall dimensions: 21 ft. 5 in. L x 32 in. W x 16 in. H.



