

**W.H. Stewart Co. Vertical Intercooler- 900 Gallon**

**Mfg: W.H. Stewart Co.**

**Model:**

**Stock No: RGMP282**

**Serial No: S-1307**

W.H. Stewart Co. Vertical Intercooler. S/N: S-1307. Nat'l Bd: 668. Approximate calculated volume capacity: 900 gallons. Inside straight-wall dimensions: 4 ft. 2 in. dia. x 9 ft. H. MAWP: 200 psig @ 650°F. Normal operating pressure: 33.5 psig. Inlets/outlets: (3) 3/4 in. dia. ports, (3) 2 in. dia. ports, (2) 8 in. dia. ports, (1) 1/2 in. dia. port, (1) 1 in. dia. port. Overall dimensions: 5 ft. 7 in. L x 4 ft. 2 in. W x 12 ft. 8 in. H.







