

1995 ABB Instrumentation Field Electro-Magnetic Flowmeter System

Mfg: ABB Instrumentation

Model: M15GA11A10R100A

Stock No. RLOL236.6

Serial No. V/88925/27/3

1995 ABB Instrumentation Field Electro-Magnetic Flowmeter System. Model: M15GA11A10R100A. S/N: V/88925/27/3. Maximum pressure: 250 psig. Process temperature: 176 °F. Ambient temperature: 140 °F. Calibration factor 1: 1.0910. Calibration factor 2/3/4: 5/9/1.000. ABB Kent-Taylor Magmaster Transmitter, Model: 00000000R100A /SEN.V/88925/27/3, S/N: V/88927/44/13, supply voltage: 95-240 VAC, frequency: 47-440 Hz. Inlets/outlets: (2) 1-1/2 in. dia. S-line fittings. Overall dimensions: 6-1/2 in. L x 3 in. W x 10 in. H. Overall dimensions (sensor): 15 in. L x 7-1/2 in. W x 11 in. H.



