

G&H Sanitary Centrifugal Pump

Mfg: G&H

Model: GHH-40

Stock No: RLOL566B.25

Serial No: 98-10-55169

G&H Sanitary Centrifugal Pump. Model: GHH-40. Serial No: 98-10-55169. Motor: Baldor Electric Co., 10 hp, 3500 rpm, 208-230/460 V, 25-23/11.5 amps, 60 Hz, 3 phase, washdown duty. Pump is currently missing the impeller. Inlet (1): 3 in. dia. S-line fitting. Outlet (1): 2 in. dia. S-line fitting. Overall dimensions: 2 ft. 1 in. L x 1 ft. 2 in. W x 1 ft. 8 in. H.







BALDOR®
WASHDOWN DUTY MOTOR

BALDOR ELECTRIC CO. FT. SMITH, AR. MFG. IN U.S.A.

CAT. NO.	CWD3711T		
SPEC.	37H879T223H1		
HP	10		
VOLTS	208-230/460		
AMPS	25-23/11.5		
R.P.M.	3500		
FRAME	215TC	HZ 60	PH 3
SER. F.	1.15	ODE H	DES B CLASS F
NSMA NOM. EFF.	89.5 %	P.F.	91 %
RATING	40C AMB-CONT		
CC	010A	USABLE AT 208V	25 A
BEARINGS	DE 6307	ODE 6206	
ENCL.	TEFC	ISN	F0604193540