

Trane Air Cooled Condenser 80 Tons

Mfg: Trane

Model: CAVCC8042B10

Stock No. 45.Rc0028

Serial No. J92E82419

Trane Air Cooled Condenser.

Trane Air Cooled Condenser 80 Ton. Model CAUCC8042B10. S/N J92E82420. Rated Voltage 460, 60 Hz, 3-Phase, Utilization Voltage Range 416-508, Nominal System Voltages 440-460-508, Min. Circuit Ampacity 15 Amps for Circuit 1, Max. Fuse Size 15, (8) Condenser Fan Motors [460 Volt, 60 Hz, 3-phase, FLA EA 18, HP EA 100], Factory Charged Refrigerant for Ckt 1 and Ckt 2 are 2 lbs of R-22 for each system. Design Pressure 450 PSIG, Test Pressure High/ Low are 450 PSIG/ 300 PSIG, respectively. Condenser contains (8) 27 in. Dia. Fans and (2) 30-1/2 in. W x 30 in. L Exhaust Ducts. Overall Dimensions: 177 in. L x 90 in. W x 89 in. H.



