

Van Steenburgh Engineering Laboratories Inc. BV Series Refrigerant Reclaim System

Mfg: Van Steenburgh Engineering Laboratories Inc.

Model: M/N BV-300-V

Stock No.: SABE040.1

Serial No.: 0690-572

Van Steenburgh Engineering Laboratories Inc. BV Series Refrigerant Reclaim System. Model: M/N BV-300-V. S/N: 0690-572. Capacity: 300 lbs. of refrigerant. Bristol Hermetic Scroll Compressor, Model: M518143BBCA, S/N: 10895027705, power supply: 208-230 V, 69 LRA, 60 Hz, single phase. Accumulator - 4 Gallon, inside straight-wall dimensions: 6 in. dia. x 2 ft. 10 in. H. Accumulator - 1/3 Gallon, inside straight-wall dimensions: 3 in. dia. x 1 ft. H. (9) Horizontal Refrigerant Receivers- 4 Gallon (ea). Evaporator dimensions: 2 ft. L x 1-1/2 in. W x 1 ft. 8 in. H. Fins per inch: 12. Phillips 1 ft. diameter fan. Inlet: (1) 1/4 in. dia. refrigerant infeed. Outlet: (1) 1/4 in. dia. refrigerant discharge. This refrigerant reclaim system is not currently operational. Overall dimensions: 6 ft. L x 2 ft. 8 in. W x 5 ft. 1-1/4 in. H.(ACN140).







