

Cherry Burrell Horizontal Insulated Holding Tank- 1,500 Gallon

Mfg: Cherry Burrell

Model:

Stock No. RLOL700.3

Serial No.

Cherry Burrell Horizontal Insulated Holding Tank- 1,500 Gallon. Propeller diameter: 16 in. Tank is equipped with a front access ladder and two sight glasses. Completely CIP'able. Master Gearmotor, 1-1/2 hp, 1725 rpm, 96 rpm (final), 208-220/440 V, 4.9/2.45 amps, 60 Hz, 3 phase. Inlets: (1) 3/4 in. dia. NPT (thermowell), (1) 1-1/2 in. dia. port (sprayball), (1) 3 in. dia. threaded fitting. Outlets: (1) 2 in. dia. S-line fitting (discharge), (1) 3 in. dia. vent. Overall dimensions: 108 in. L x 95 in. W x 106 in. H.





