

FMC FoodTech Stainless Steel Vegetable Washer

Mfg: FMC / JBT Food Tech

Model: Ultra Direct

Stock No.: SAFC01.

Serial No.: F72741

FMC / JBT FoodTech Washer. Model: A3C0114-3. Designed to wash, drain, and convey vegetables. Basic operation: product infeed at hopper, adjust hopper discharge rate with slide, product is conveyed via adjustable speed vibratory conveyor, conveyor floor is a screen, (3) water spray bars above conveyor, V-bottom pan below catches the water, product exits end opposite the infeed. FMC FoodTech Newberg Vibrating Conveyor. Model: Ultra Direct. F.O.: F72741. Dwg. No.: F72741D002. Speed: 1194. Stroke: .25. Vibrator motors (2): 230V, 4.4 amps, 3-phase, 60 Hz. Lesson Speedmaster Washguard adjustable motor controller: 240V, 60 Hz, 3-phase. Hopper dimensions: 48 in. L x 35.75 in. W x 27 in. H. Hopper gate to conveyor opening: 21 in. W x 14 in. H. Conveyor dimensions: 75.5 in. L x 23.25 in. W x 5 in. H. Overall dimensions: 127 in. L x 55 in. W x 51 in. H.









