

BAC VXMC-860-H Evaporative Condenser - 860 Tons

Mfg: BAC

Model: VXMC-860-H


Stock No: RPCA1369M.45

Serial No:

BAC VXMC-860-H Evaporative Condenser. 860 nominal tons using R-22 at a 105°F condensing temperature, a 40°F suction temperature, and a 78°F wet-bulb temperature. 610 tons using R-717(ammonia) at a 96.3°F condensing temperature, a 20°F suction temperature, and a 78°F wet-bulb temperature. (6) fans. (2) 5 hp pumps. Belt: 6-B144. Shipping Weight: 44,740 lbs (15,240 lbs heaviest). Overall Dimensions: 35 ft. 9-1/4 in. L x 9 ft. 10-1/8 in. W x 13 ft. 1-7/8 in. H.







CATALOG # UJ5S2AM MODEL # B075
 SRAFT END BRG 6307-22JC3 SFP END BRG 6205-22JC3
 FR 184JM TYPE UT-4 ENCL TE
 PH 3 MAX 40 °C IDW J07-B075-M
 DUTY CONT WT

HZ 60	HP 5.00	RPM 1745	SF
SF 01 25	DESIGN B	CODE J	
VOLTS 208-230/460		FLAMPS 15.00-13.70/6.85	
SF AMPS 16.60/8.30		AMP MAX 16.20 AT 208V 60HZ	

CATALOG # UJ5S2AM MODEL # B075
 SRAFT END BRG 6307-22JC3 SFP END BRG 6205-22JC3
 FR 184JM TYPE UT-4 ENCL TE
 PH 3 MAX 40 °C IDW J07-B075-M
 DUTY CONT WT

HZ 60	HP 5.00	RPM 1745	HZ 50
SF 01 25	DESIGN B	CODE J	SF
VOLTS 208-230/460		FLAMPS 15.00-13.70/6.85	
SF AMPS 16.60/8.30		AMP MAX 16.20 AT 208V 60HZ	

MADE IN MEXICO
 U.S. ELECTRICAL MOTOR DIVISION OF EMERSON ST LOUIS MO
 422702-003



Installed Pics:

