

Bran+Luebbe Auto In-line Blend System with 4 Metering Pumps

Mfg: Bran+Luebbe

Model: N-C34-K31

Stock No: SCJC181.5a

Serial No: A1500

Bran+Luebbe Auto In-line Blend System with 4 Metering Pumps. Type: N-C34-K31. Machine no. A1500. Approximate capacities: "A" pump: 24 gpm, "B" pump: 13 gpm, "C" pump: 4 gpm, and "D" pump: 3 gpm. Product contact surfaces: 316 stainless steel. Working pressure: 90 psi. Metering pumps address products that need to be blended and metered to include light to heavily viscous food products. This unit was previously in service pumping varieties of syrups and fruit concentrates. Baldor industrial motor: 5 hp, 870 rpm, 230/460 v, 18.8/9.4 a, 60 Hz, 3 phase. (1) Hubbell® disconnect switch: Cat no. HBLDS3, 30 amp, 600 VAC max. Inlets/outlets: (4) 2 in. outer dia. and 7/8 in. inner dia. tri-clamp, (4) 2 in. S-line. Overall dimensions: 4 ft. 7-1/2 in. L x 2 ft. 7 in. W x 5 ft. 9 in. H.





