

## Vilter VSS-1201 Single Screw Ammonia Compressor - 200 hp

Mfg: Vilter

Model: VSS1201A02531APAAAN

Stock No: RPCN074.30

Serial No: 1979

1994 Vilter VSS-1201 Single Screw Ammonia Compressor Package. Model: VSS1201 A025231APAAAN. S/N: 1979. Order Number: K18461. Refrigerant: Last used with R-717 (ammonia). Nominal capacity: 127.6 tons at 127.6 bhp with a -40°F suction temperature and a 20°F condensing temperature. Variable Vi setting. Displacement: 1,193 cfm. Test pressure: 350 psig. Baldor electric motor. 200 hp, 3560 rpm, 460 V, 217 amps, 60 Hz, 3 phase. 1994 Vilter oil separator. S/N: 3-63807-1. National Board: 40138. MAWP: 300 psig @ 400°F. MDMT: -5°F @ 300 psig. Straight-wall dimensions: 2 ft. 6 in. dia. x 12 ft. 9 in. L. Nominal capacity: 490 gallons. Viking pump. Model: HV2994. S/N: 10828747. Marathon electric motor. 1-1/2 hp, 1430 rpm, 160/280 V, 5.4/2.7 amps, 60 Hz, 3 phase. Vilter Microprocessor control panel. Inlet: (1) 5 in. dia. (refrigerant suction). Outlet: (1) 5 in. dia. (refrigerant suction). Current display reading is 18453.03 hours. Estimated shipping weight: 7,970 lbs. Overall dimensions: 14 ft. 2 in. L x 5 ft. W x 8 ft. 4 in. H.

Westinghouse Motor Starter Control Panel - 200 HP. Cat. No: R896S5AW1X F940429. Dwg: VW12331. Mods: C702T2. Ref. No: 022988. Power supply: 460 V, 225 FLA, 60 Hz, 3 phase.







