

3M Model 800a Case Sealer

Mfg: 3M

Model: 800a

Stock No: SFEC3907.1

Serial No: 5702

3M Case Sealer. Model no. 800a. Serial no. 5702. Type: 39600. Capacity: 40 cases per minute. Maximum width and height: 1 ft. 7-1/2 in. (2) Bodine Electric Co. motor: Type no. 42X5BFCI-E2. 1/6 Hp, 115 rpm, 115 V, 1.9 A, 60 Hz, 1 phase, 68 lb-in torque, 15:1 ratio. Case sealer handles 6 in. and up in length. Min/max width of box: 4-1/2 in. to 1 ft. 7-1/2 in. Min/max height of boxes: 4-3/4 in. to 2 ft. 1 in. Features include: spring-loaded side drives to center cases, dual masts with dual lead mast screws for extra stability and uniform height adjustments, twin gear drive motors for heavy-duty reliability, and 3 taping heads for low-impact, top and bottom tape applications. Overall dimensions: 4 ft. 6 in. L. x 3 ft. 3 in. W. x 5 ft. 8 in. H.





