

Bursa Fill Controlled Volume Packaging Pump System

Mfg: Bursa

Model:

Stock No. SAPM020.1

Serial No. 5-A4775

Bursa Fill Controlled Volume Packaging Pump System. S/N: 5-A4775. Infeed hopper diameter: 17-1/2 in. Westinghouse Motor, 3/4 hp, 1,725 rpm, 115/230 V, 10/5 amps, single phase. Boston Gear Reducer, 15 ratio, 116.67 rpm (final), 268 in. lb. torque. Inlets: 3 in. L x 1-1/2 in. H. Outlets: (1) 1-1/2 in. dia. threaded fitting. Overall dimensions: 33 in. L x 19 in. W x 36 in. H.

(2) Sensors, Model MK2PN-S, electrical requirements: 120 VAC, 250 VAC/28 VDC, 10 amps (Res), 250 VAC, 7A (Gen).

