

## Philadelphia Mixers Agitator MT Mixing Drive

Mfg: Philadelphia Mixers

Model: PTO

Stock No. SELM162.a

Serial No. 80BAJ1143-44

Philadelphia Mixers Agitator MT Mixing Drive. Model: PTO. S/N: 80BAJ1143-44. Order No: 832686-P. Agitator shaft diameter: 2 in. Coupling shaft dimensions: 2 in. dia. x 17 in. L. Reliance Motor, 5 hp, 1730 rpm, 56 rpm (final), 230/460 V, 14/7 amps, 31.4 gear ratio 60 hz, 3 phase. Overall Attachment flange dimensions: 11 in. dia. with (8) 3/4 in. dia. attachment holes at a center-to-center distance of 9-1/2 in. Features include: 304 stainless steel wetted parts and size MT-02(FM), double reduction, right angle shaft design. Chuck drive max. dimensions: 27-1/2 in. L x 14 in. W x 27 in. H.





