

## Bock Engineered Products Inc. Centrifuge Dryer

**Mfg: Bock Engineered Products Inc.**

**Model: FP-35**

**Stock No: SFEC3917A.5a**

**Serial No: NA / FP35-1052**

Bock Engineered Products Inc. Centrifuge Dryer. Model: FP-35. Unit 1 S/N: NA. Unit 2 S/N: FP35-1052. Rated maximum basket capacity: 35 lbs. Rated maximum basket speed: 800 rpm. Spinner / basket holder dimensions: 1 ft. 6 in. dia. x 1 ft. 1 in. H. Unit 1 has a Leeson motor: 2 hp, 1740 rpm, 208-230/460 V, 6/3 A, 60 hz, 3 phase. Unit 2 has a Baldor motor: 2 hp, 1740 rpm, 230/460 V, 5.6/2.8 A, 60 hz, 3 phase. Emergency stop button. Pneumatic operated door. Inlet: (1) 2 ft. 2 in. L x 2 ft. 1-3/8 in. W door. Outlets: (2) 2 in. port. Shipping weight: 625 lbs. Overall dimensions: 3 ft. 5 in. L x 2 ft. 6 in. W x 3 ft. 9-1/4 in. H.





