

## Compression Roller System for Cereal Bars

Mfg:

Model:

Stock No. SGMPB011.11a

Serial No.

Compression Roller System for Cereal Bars. (6) Upper rollers: 40-1/2 in. L x 6 in. dia. Upper rollers with hand wheel adjustment. (1) Lower roller: 44 in. L x 11 in. dia. Inlet height: 40 in. (adjustable) Outlet height: 34 in. (adjustable) Reliance Electric Motor, 1/2 hp, 1725 rpm, 208-230/460 V, 1.5-1.5/0.75 amps, 60 Hz, 3 phase. Dodge motor drive: ratio: 125, output: 13.8 rpm. Allen-Bradley, Guard Master emergency stop. Overall dimensions: 13 ft. L x 62 in. W x 66 in. H.

(6) Reliance electric motors, 1/2 hp, 1725 rpm, 208-230/460 V, 1.5-1.5/0.75 amps, 60 Hz, 3 phase. (6) Dodge motor drives, ratio: 125, output: 13.8 rpm. Eckels-Bilt belt tensioner.



