

2000 Waukesha Cherry-Burrell Votator Scraped Surface Heat Exchangers

Mfg: Waukesha Cherry-Burrell

Model:

Stock No.: SGM4158.9


Serial No.: A6723

2000 Waukesha Cherry-Burrell Votator Scraped Surface Heat Exchangers- 6 x 72. S/N: A6723. Shell MAWP: 600 psi @ 400°F. Jacket MAWP: 250 psi @ 400°F. Heat transfer surface area: 9 sq. ft. Siemens Motor, 15 hp, 1770 rpm, 230/460 V, 38.4/19.2 amps, 60 Hz, 3 phase. Speed Reducer. Votator scraped surface heat exchangers can process virtually any pump able fluid or slurry: they can cook, heat, cool, slush, freeze, pasteurize, sterilize, aerate, mix, extrude, crystallize, gel, plasticize, emulsify, or polymerize. The design consists of a concentric shaft and uses (24) Teflon scrapers. Inlets: (1) 3 in. dia. I-Line fitting (product), (1) 1-1/2 in. dia. (media). Outlets: (1) 3 in. dia. I-Line fitting (product), (1) 1-1/2 in. dia. (media). Overall dimensions: 9 ft. 7 in. L x 2 ft. 3-1/2 in. W x 4 ft. 10 in. H.









SIEMENS 3-Phase Type 1 LA7163-4BA99-ZR91
 E0008/121010 01 011
 Frame 160M Const. IP
 230/430v YYY 38,4/19,2 amp
 11,0 kW SER.F1,15
 0,82pf Ins.CL F
 60 Hz 1770rpm Amb. 40°C
 Encl. TE C-17171110/0026 15,0HP

Waukesha
 Cherry-Burner
 A United Technologies Company

SHELL	M.A.W.P. 600 PSI at 400 F	F
	M.D.M.T. - 20 F at 600 PSI	
JACKET	M.A.W.P. 250 PSI at 400 F	F
	M.D.M.T. - 20 F at 250 PSI	
MFG. SER. NO.	A 8723	
YEAR BUILT	2000	