

## 1995 DCA Gas Fryer

Mfg: DCA

Model: RFC 334 DE

Stock No. SGMT265.9

Serial No. 113

1995 DCA Gas Fryer. Model: RFC 334 DE. S/N: 113. Stainless steel. (8) Heat tubes: 24 in. L x 2 in. diameter. Container: 24 in. L x 34 in. W x 7-1/2 in. H. Container oil capacity: 23 gallons for high level, 19.5 gallons for low level. (2) Fryer screens: 23 in. x 33 in. Screen mesh: 0.20 in. Flow control valve with four settings: 1/4 in., 1/2 in., 3/4 in. and close. Controls: 120 V, 50/60 Hz, 1 phase. Switch on/off, reset button, manual temperature controller: 390°F to 200°F. Portable table dimensions and fryer cover: 28 in. x 29-1/2 in. Inlet gas: 1 in. threaded male. Steam outlet dimensions: 3-3/4 in. x 16-1/2 in. Overall dimensions: 44 in. L x 41 in. W x 61 in. H.



